



elesa  
Original design MSP.

1 l <sub>1</sub>	2 d <sub>1</sub>	2 d <sub>2</sub>	a	b <sub>1</sub>	b <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub> ±0,5	t <sub>1</sub>	t <sub>2</sub>	F <sub>1</sub> in N		F <sub>2</sub> in N	
											M6	B4,5	M6	B4,5
100	M 6	B 4,5	10	13	38	30	21	80	10	14	3000	700	1900	900

**Specification**

**Handle**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +100 °C
- Black-gray, RAL 7021, matte finish

**Threaded bushing**

Brass

RoHS

Ledge handles GN 130 with bore hole B 4,5 are intended for fixing with self-tapping screws of thread size ST 4,8 such as pan head self-tapping screws DIN ISO 7049.

The forces F<sub>1</sub> and F<sub>2</sub> given in the table are failure loads, which means that the appropriate safety factor must be taken into account. No liability is otherwise accepted for the reference values given. They do not constitute a warranty of quality. The user must determine from case to case whether the handle strip is suitable for the intended purpose. Ambient factors and ageing processes may influence the given values.

see also...	Page
GN 730 Ledge Handles (Aluminum)	QVX
GN 430 Ledge Handles (Aluminum)	QVX

**Technical Information**

Strength Properties	QVX
Plastic Characteristics	QVX

How to order	
1	l <sub>1</sub>
2	d <sub>2</sub> (d <sub>1</sub> )
3	Color

**GN 130-100-B4,5-SG**