



4 Type

- D Straight lever
- E Angled lever

- 1
- 2
- 3

d ₁	d ₂	l ₁								d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈	h ₅ Stroke	l ₂
32	M 8	12	16	20	25	32	40	50	63	13,5	8	20	20,5	1,5	12,5	36	4	100
32	M 10	20	25	32	40	50	63	80	-	13,5	8	20	20,5	1,5	12,5	36	4	100
36	M 10	16	20	25	32	40	50	63	80	16	10	25	24,5	2	15	45	4,5	120
36	M 12	25	32	40	50	63	80	-	-	16	10	25	24,5	2	15	45	4,5	120
40	M 12	25	32	40	50	63	80	-	-	19	12	30	26,5	2	16	50	4,5	130
45	M 16	32	40	50	63	80	-	-	-	23	12	32	31,5	2	20	60	5	145

Specification

- Steel
Blackened
Threaded stud
Property class 5.8
- Cover
Plastic, light gray
- Ball knobs DIN 319
Plastic, Duroplast
Black, shiny finish
- Safety circlip
Plastic (Polyacetal)
- Strength Values of Screws → Page 2152
- Plastic Characteristics → Page 2158
- RoHS

Information

The overall height of flat adjustable tension levers GN 125 is reduced to a minimum.

As all other adjustable levers, they are ideal whenever parts have to be clamped in a confined space, or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and the lever can be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

- Flat Adjustable Stainless Steel Tension Levers GN 125.5 → Page 487
- Flat Adjustable Tension Levers GN 126 (Threaded Stud, Steel) → Page 489

On request

- With inch threads

How to order		1	d ₁
		2	d ₂
GN 125-32-M8-40-E		3	l ₁
		4	Type