



l ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
	M 8	M 10	M 12	B 8	B 10							
120	M 8	M 10	M 12	B 8	B 10	16	32	29,5	2	41,5	2,5	14
145	M 12	M 16	-	B 12	B 16	23	40	42	4	56	4	22

Specification

- Handle
Zinc die casting
- Powder coated
Black, RAL 9005, textured finish ● **SW**
Silver, RAL 9006, textured finish ○ **SR**
- Hub cover
Plastic
- Black for SW
- Light gray for SR
- Countersunk screw
Stainless steel
- Chemically blackened for SW
- Plain for SR
- GN 126**
Threaded bushing / bore bushing
Steel, blackened
- GN 126.1**
Threaded bushing / bore bushing
Stainless steel AISI 303
- [ISO Fundamental Tolerances](#) → Page 2151
- [Stainless Steel Characteristics](#) → Page 2166
- RoHS

On request

- With inch threads

Information

Flat adjustable tension levers GN 126 / GN 126.1 are characterized by their low height and the timelessly elegant design.

They are ideal whenever swiveling in a confined space is required or the lever is to be clamped in a particular position. The threaded insert / bored bushing is moveably attached to the handle with serrations.

Pulling the lever disengages the serrations, allowing it to be swiveled to the ideal clamping position. On “releasing” the handle, the serrations re-engage automatically.

see also...

- Adjustable Hand Levers GN 300 (Bushing Steel) → Page 428
- Adjustable Hand Levers GN 300.1 (Bushing Stainless Steel) → Page 438
- Adjustable Stainless Steel Hand Levers GN 300.5 (Matte Shot-Blasted) → Page 440
- Flat Adjustable Hand Levers GN 302 → Page 448
- Flat Adjustable Tension Levers GN 125 (Bushing Steel) → Page 484
- Flat Adjustable Stainless Steel Tension Levers GN 125.5 → Page 486

How to order (Bushing steel)

GN 126-120-M10-SR

- | | |
|---|----------------------------------|
| 1 | l ₁ |
| 2 | d ₁ (d ₂) |
| 3 | Color |

How to order (Bushing stainless steel)

GN 126.1-145-M12-SW

- | | |
|---|----------------------------------|
| 1 | l ₁ |
| 2 | d ₁ (d ₂) |
| 3 | Color |