



- 3 Identification no.**
- 2** With 2 stainless steel socket cap screws DIN 912

d₁ Bore		d₂ Bore		k Clamping length	l₁	m	z Screw locations	Accessory Recommended hand lever for z			
Aluminum	Stainless steel	Aluminum	Stainless steel					GN 911 for aluminum l₂		GN 911.3 for stainless steel l₂	
B 10	-	B 10	-	25	64	20	M6-20	63	-	-	-
B 12	B 12	B 12	B 12	25	64	20	M6-20	45	63	-	-
B 14	B 14	B 14	B 14	25	64	20	M6-20	45	63	-	-
B 15	B 15	B 15	B 15	25	64	20	M6-20	45	63	-	-
B 16	B 16	B 16	B 16	25	64	20	M6-20	45	63	-	-
B 18	B 18	B 18	B 18	25	64	20	M6-20	45	63	45	63
-	B 20	-	B 20	25	64	20	M6-20	-	-	45	63

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Plain, matte shot-blasted ○ **BL**
- Stainless steel AISI CF-8 **NI**
Matte shot-blasted
- Socket cap screws DIN 912
Stainless Steel AISI 304
- Hex nuts DIN 985
Stainless Steel AISI 304
Self-locking via polyamide ring
- [Stainless Steel Characteristics](#) → Page 2166
- **RoHS**

Accessory

- Adjustable Hand Levers GN 911 / GN 911.3
→ Page 1784 / 1785

On request

- d₁ / d₂ with unequal bores

Information

The clamping bores of two-way connector clamps GN 131 are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 / GN 911.3 listed in the table as accessories.

see also...

- [Two-Way Mounting Clamps GN 474](#) → Page 1791
- [Construction Tubes GN 990](#) → Page 1835
- [Retaining Rods / Retaining Tubes GN 480.1](#) → Page 1833
- [Linear Actuator Connectors GN 131.1 / GN 131.2](#) → Page 1954

How to order (Aluminum)

GN 131-B14-B14-2-SW

1	d ₁
2	d ₂
3	Identification no.
4	Finish

How to order (Stainless steel)

GN 131-B18-B18-2-NI

1	d ₁
2	d ₂
3	Identification no.
4	Material