




¹ d ₁	² d ₂	k	l ₁	l ₂	m	s ₁ Square	s ₂ Square	z ₁ Screw location	z ₂ Screw location
B 12	B 12	12	36,5	25	14	10	10	M4-12	M4-12
B 20	B 12	20	51	42	20	16	10	M6-20	M6-12
B 20	B 20	20	57	42	22	16	16	M6-20	M6-18

Specification

Connector clamp
Stainless steel AISI CF-8
Matte shot-blasted

Socket cap screws ISO 4762
Stainless steel

RoHS

⁴

The clamping bores of the two-way connector clamps GN 131.3 are designed for typical construction tubes. The square sections s₁ and s₂ also allow bars or tubes with a square cross-section to be clamped.

At the screw locations z₁ and z₂, socket cap screws reduce the bore cross-section for clamping. The split clamping point z₂ allows the connector clamp to be subsequently inserted into an existing structure and facilitates assembly when axial sliding is not possible, e.g., due to tight bending radii.

see also...

ganternorm.com

GN 131 Two-Way Connector Clamps (Aluminum / Stainless Steel, Single Part)

GN 474 Two-Way Connector Clamps (Aluminum, Single Part)

GN 131.4 Two-Way Connector Clamps

Technical Information

Stainless Steel Characteristics

Accessory

GN 990 Construction Tubes

How to order	1	d ₁
	2	d ₂
	3	Identification no.
	4	Material
GN 131.3-B20-B12-2-NI		