


- 3 Identification no.
- 2 With 3 socket cap screws
ISO 4762

1 d ₁	2 d ₂	k	l ₁	l ₂	m	s ₁ Square	s ₂ Square	z ₁ Screw location	z ₂ Screw location
B 12	B 12	20	35,5	42	14	10	10	M6-8	M6-12
B 12	B 20	20	44,5	42	17	10	16	M6-10	M6-18

Specification

4

Connector clamp

Stainless steel AISI CF-8

Matte shot-blasted

NI

Socket cap screws ISO 4762

Stainless steel

RoHS

The clamping bores of the two-way connector clamps GN 131.4 are designed for typical construction tubes. The square sections s_1 and s_2 also allow bars or tubes with a square cross-section to be clamped. Clamping at screw point z_1 is performed radially on the surface of the profiles used. At the screw location z_2 , socket cap screws reduce the bore cross-section for clamping. The split clamping point z_2 allows the connector clamp to be subsequently inserted into an existing, structure and facilitates assembly when axial sliding is not possible, e.g., due to tight bending radii.

see also...

ganternorm.com

GN 131 Two-Way Connector Clamps (Aluminum / Stainless Steel, Single Part)

GN 474 Two-Way Connector Clamps (Aluminum, Single Part)

GN 131.3 Two-Way Connector Clamps

Technical Information

Stainless Steel Characteristics

Accessory

GN 990 Construction Tubes

How to order	1 d ₁
	2 d ₂
	3 Identification no.
	4 Material
GN 131.4-B12-B12-2-NI	