



**elesa**  
Original design TCC-CR / TCC-CR-VD



- 4 Identification no.**
- 2 With 2 stainless steel socket cap screws ISO 4762

<b>1</b> $d_1$ Bore	<b>2</b> $d_2$ Bore	<b>3</b> $k$ Clamping length	$l_1$	$m$	$z$ Screw locations	<b>Accessory</b> Recom. hand lever GN 911.9 for $z$	
						$l_2$	
B 18	B 18	29	65	19,8	M6-18	44	63
B 30	B 30	45	100,5	34,6	M8-25	63	78

**Specification**

**Connector clamp**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -20 °C to +100 °C
- Color
  - Black, RAL 9005, matte finish
  - Gray, RAL 7040, matte finish
  - Blue, RAL 5005, matte finish
- FDA compliant material
- Visually detectable

- S
- G
- V

**Socket cap screws ISO 4762**

Stainless steel AISI 304

**Hex nuts DIN 985**

Stainless steel AISI 304

Self-locking with polyamide ring

RoHS

**Accessory**

**Page**

<b>GN 990</b> Construction Tubes (Aluminum / Stainless Steel)	QVX
<b>GN 290</b> Adapter Bushings	QVX
<b>GN 911.9</b> Adjustable Hand Levers	QVX

The clamping bore axes of the two-way connector clamps GN 132.9 are arranged at an angle of 90° to each other. They hold typical construction tubes with full surface contact over the entire cross-section of the bore.

At the screw locations  $z$ , the socket cap screws reduce the bore cross-section for clamping. Adapter bushings GN 290 can be used to reduce the bore cross-sections to a smaller diameter.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911.9 listed in the table as accessories.

The plastic used in version V is made from blue, visually detectable and FDA-compliant plastic granulate as per FDA CFR.21 and EU 10/2011.

**see also...**

	<b>Page</b>
<b>GN 132</b> Two-Way Connector Clamps (Aluminium)	QVX
<b>GN 132.5</b> Two-Way Connector Clamps (Stainless Steel)	QVX

**Technical Information**

Load Rating Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

**How to order**

<b>1</b>	$d_1$
<b>2</b>	$d_2$
<b>3</b>	$k$
<b>4</b>	Identification no.
<b>5</b>	Color

**GN 132.9-B30-B30-45-2-S**