


3 Identification no.

- 2 With 4 stainless steel socket cap screws DIN 912



Adjustable hand levers
GN 911

1

1

1

2

d₁ - d₂ Bore - Bore	d₁ - s₂ Bore - Square	s₁ - s₂ Square - Square	k Clamping length	l₁	l₂	m	z Screw locations	Accessory Recom. hand lever GN 911 for z l₃
B20 - B20	B20 - V20	V20 - V20	50	79,5	68	33,5	M8-30	63 78
B25 - B25	B25 - V25	V25 - V25	50	79,5	68	33,5	M8-30	63 78
B30 - B30	B30 - V30	V30 - V30	50	79,5	68	33,5	M8-30	63 78
B30 - B30	B30 - V30	V30 - V30	60	109	79	50	M8-50	63 78
B32 - B32	-	-	60	109	79	50	M8-50	63 78
B35 - B35	B35 - V35	V35 - V35	60	109	79	50	M8-50	63 78
B40 - B40	B40 - V40	V40 - V40	60	109	79	50	M8-50	63 78
B40 - B40	B40 - V40	V40 - V40	76	125	98	55	M10-50	78 92
B42 - B42	-	-	76	125	98	55	M10-50	78 92
B45 - B45	B45 - V45	V45 - V45	76	125	98	55	M10-50	78 92
B48 - B48	-	-	76	125	98	55	M10-50	78 92
B50 - B50	B50 - V50	V50 - V50	76	125	98	55	M10-50	78 92

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Plain, matte shot-blasted **○ BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- Stainless Steel Characteristics* → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

4

Information

The clamping bores of two-way connector clamps GN 134 are not machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462 .

The versions with square bores are also suitable for use with **profile systems**.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

see also...

- Product Family Standard Parts for Profile Systems* → Page 18
- Construction Tubes GN 990* → Page 1835
- Two-Way Linear Actuator Connectors GN 134.1* → Page 1978

How to order

1	d ₁ - s ₂ (d ₁ - d ₂ , s ₁ - s ₂)
2	k
3	Identification no.
4	Finish

GN 134-B45-V45-76-2-SW