



3 Type

- G** With thread
- R** With indexing plunger
- D** With spring plunger



Adjustable hand levers GN 911
Construction tube with locking holes GN 990.1

1

2

s ₁ Square	s ₂ Square	d ₁	d ₂ Pin -0,05 Bore +0,03 -0,08	d ₃ Ball Ø	k Clamping length	l ₁	l ₂	m	z Screw locations	Accessory Recom. hand lever GN 911 for z l ₃	
V 25	V 25	M 8	5	3,5	50	79,5	68	33,5	M8-30	63	78
V 30	V 30	M 8	5	3,5	50	79,5	68	33,5	M8-30	63	78
V 40	V 40	M 12	8	6,5	76	125	98	55	M10-50	78	92
V 50	V 50	M 12	8	6,5	76	125	98	55	M10-50	78	92

Specification

4

- Aluminum
Powder coated
Black, RAL 9005, textured finish ● **SW**
- Fastening elements / transfer elements
 - Socket cap screws DIN 912
 - Hex nuts DIN 985
 - Centering bushings
Stainless steel AISI 304
- Indexing plunger GN 717, type CK
 - Plunger pin
Stainless steel AISI 303
 - Knob
Plastic (Polyamide PA)
Black, matte finish
- Spring plunger GN 615.9, type KN
 - Stainless steel AISI 303
 - Ball with friction bearing
 - With internal hex
 - Stainless steel lock nut ISO 4035
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

Information

With two-way locking slide units GN 134.7, recurring positions along a square construction tube can be moved to easily and quickly. The required holes for type R or countersinks for type D can be created by the user according to the design instructions or ordered as completely finished construction tubes with locking holes GN 990.1.

For quick clamping without tools, the socket cap screws at the screw locations z, can be replaced by the adjustable hand levers GN 911 listed in the table as accessories. Centering bushings in the pass-through holes eliminate the axial play between the top and bottom parts of the locking slide units.

Two-way locking slide units GN 134.7 are delivered with unmounted indexing plunger (Type R) or spring plunger (Type D). Type G with thread is universally suitable for specific applications.

see also...

- *Construction Information and Application Examples* → Page 1975
- *Construction Tubes with Locking Holes GN 990.1* → Page 1977
- *Construction Tubes GN 990 (Square, without Locking Holes)*
→ Page 1835
- *Square Linear Actuators GN 291.1* → Page 1973

How to order

1	s ₁
2	s ₂
3	Type
4	Finish

GN 134.7-V40-V40-R-SW