



- 4 Type**
- A** Without bores (only in stainless steel NI)
 - B** With through-holes
 - C** With countersunk holes

2		3											
l ₁		l ₂	d ₁	d ₂	d ₃	d ₄	m ₁		m ₂	m ₄	m ₅	s	
On one side elongated	On both sides elongated						On one side elongated	On both sides elongated					
45	60	30	3	3,2	4	6,4	33	48	18	9	24	1,5	
60	80	40	4	4,2	5	8,3	45	65	25	12,5	32,5	2	
75	100	50	6	5,2	5	8,3	55	80	30	15	40	2	
90	120	60	6	5,2	5	8,3	66	96	36	18	48	2	

Specification

Hinge leafs

- Steel **ST**
- Zinc plated, blue passivated
- Only type B / C
- Stainless steel AISI 304 **NI**
- Plain finish
- All types
- Powder coated
- Black, RAL 9005, textured finish **NISW**
- Only type B
- Stainless steel AISI 316 **A4**
- Only type B / C

Pin

- Stainless Steel
- AISI 304 for ST / NI / NISW
- AISI 316 for A4
- Riveted

RoHS

Sheet metal hinges GN 136 are available in many different versions and are suitable for light to medium-duty applications.

Type A can be fixed in place by welding or by using holes made by the customer.

The stainless steel versions are particularly suited for applications in highly aggressive conditions.

see also...	Page
GN 136 Sheet Metal Hinges (Steel / Stainless Steel, Square or Vertically Elongated)	QVX
GN 1362 Sheet Metal Hinges (Stainless Steel, for Welding)	QVX
GN 1364 Sheet Metal Hinges (Stainless Steel, Pointed)	QVX
GN 1366 Hinges (Steel Profile, for Welding)	QVX

Technical Information

List of Hinge Types	QVX
Load Rating Information of Metal Hinges	QVX
Stainless Steel Characteristics	QVX

How to order		1	Material
		2	l ₁
		3	l ₂
		4	Type
GN 136-ST-60-40-B			