


4 Type

A Mounting from the back

Swiveling range



2

3

l ₁	l ₂		d ₁	d ₂	h ₁	h ₂	l ₃	l ₄	l ₅	l ₆	m ₁	m ₂	m ₃	t
	Short	Long												
40	42	65	M 5	5	15	9	34	54	12	18	25	25	22,5	6
50	52	80	M 6	6	19,5	11,5	39	64	16	21	30	30	27,5	8
60	62	95	M 6	8	23,5	13,5	47	77	20	24	36	36	33	9
80	82	125	M 8	10	29	17	64	104	24	32	50	50	45	12

Specification

1

5

- Hinge leaf
Zinc die casting **ZD**
Powder coated
- Black, RAL 9005, textured finish ● **SW**
- Silver, RAL 9006, textured finish ● **SR**
- Pin
Stainless steel AISI 303
- Load Rating Information → Page 2121
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

With their attractive design, hinges GN 138 are suitable for use in plant and machinery where a well-designed and stylish appearance is important.

The concealed and tamper-proof mounting from the rear highlights and enhances the special appearance of the hinge.

The hole spacings of the mounting holes m₁ and m₂ of the short version match typical hinges available on the market to allow use as a replacement hinge.

see also...

- List of Hinge Types → Page 1284 ff.
- Hinges GN 237 (Zinc Die Casting) → Page 1292
- Hinges GN 237.1 (Plastic) → Page 1296
- Stainless Steel Heavy Duty Hinges GN 237.3 → Page 1294
- Hinges GN 235 (Zinc Die Casting, Adjustable) → Page 1374

How to order

1	Material
2	l ₁
3	l ₂
4	Type
5	Color

GN 138-ZD-60-95-A-SR