


4 Type
A With threaded blind bores

Swiveling range



2 3

l₁	l₂ short	l₂ long	d₁	d₂	h₁	h₂	l₃	l₄	l₅	l₆	m₁	m₂	m₃	t
40	42	65	M 5	5	15	9	34	54	12	18	25	25	22,5	6
50	52	80	M 6	6	19,5	11,5	39	64	16	21	30	30	27,5	8
60	62	95	M 6	8	23,5	13,5	47	77	20	24	36	36	33	9
80	82	125	M 8	10	29	17	64	104	24	32	50	50	45	12

Specification

- Zinc die casting
Powder coated
Black, RAL 9005, textured finish
Silver, RAL 9006, textured finish
- Pin
Stainless steel AISI 303
- *Load Rating Information → Page 2121*
- *Stainless Steel Characteristics → Page 2166*
- RoHS

1 5 ZD SW SR

Information

With their attractive design, hinges GN 138 are suitable for use in plant and machinery where a well-designed and stylish appearance is important.

The concealed and tamper-proof mounting from the rear highlights and enhances the special appearance of the hinge.

The hole spacings of the mounting holes m_1 and m_2 of the short version match typical hinges available on the market to allow use as a replacement hinge.

see also...

- *List of Hinge Types → Page 1284 ff.*
- *Hinges GN 237 (Zinc Die Casting) → Page 1292*
- *Hinges GN 237.1 (Plastic) → Page 1296*
- *Stainless Steel Heavy Duty Hinges GN 237.3 → Page 1294*
- *Hinges GN 235 (Zinc Die Casting, Adjustable) → Page 1374*

How to order

1	Material
2	l_1
3	l_2
4	Type
5	Color

GN 138-ZD-60-95-A-SR