


- 2 Identification no.
- 2 With 2 stainless steel socket cap screws DIN 912



d ₁ Bore	s Square	d ₂	d ₃ Mounting screws on the drive key	k Clamping length	l ₁	l ₂	m	t	x ₁	x ₂	y ₁	y ₂	z Screw locations	Accessory Recom. hand lever GN 911 for z l ₃	
B 30	V 30	6,5	M 4	50	53	68	30	7	50	35	75	60	M8-40	63	78
B 40	V 40	11	M 5	76	81,5	98	46,5	14	76	50	115	90	M10-65	78	92
B 50	V 50	11	M 6	76	81,5	98	46,5	14	76	50	115	90	M10-65	78	92

Specification

- Linear actuator connector
Aluminum
Powder coated
Black, RAL 9005, textured finish ● SW
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 911 → Page 1784



Information

Flanged linear actuator connectors GN 147.1 are based on flanged connector clamps. The additionally provided mounting holes are used to connect to the drive key of a linear actuator.

With the screw location z, the play of the guide bores d₁ / s can be adjusted or the linear actuator connectors can be clamped after adjustment.

For quick clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

see also...

- *Linear Actuators GN 291* → Page 1950
- *Linear Actuators GN 292* → Page 1952
- *Linear Actuators GN 293* → Page 1953
- *Square Linear Actuators GN 291.1* → Page 1973

How to order

GN 147.1-B50-2-SW

1	d ₁ (s)
2	Identification no.
3	Finish