


Socket cap screw with internal hex DIN 912



Gear lever handle GN 310



Rostfrei Inox
Stainless Steel

d₁	d₂ Bore		b₁ ±0,2	b₂	d₃	d₄ Gear lever handle	Length l	t min.
24	B 10	B 12	15,5	13	M 8	10	36	11
28	B 12	B 14	17,5	15	M 10	12	41	14
32	B 14	B 16	19,5	17	M 12	14	45	16

Specification

- **GN 150**
 - Steel, sintered
 - Black oxidised with vapor
 - Socket cap screw DIN 912
 - Steel, plain
- **GN 150.5**
 - Stainless steel AISI 316LHC
 - Sintered
 - Socket cap screw DIN 912
 - Stainless steel AISI 304
- *ISO Fundamental Tolerances* → Page 2151
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

Split hubs GN 150 / GN 150.5 are distinguished by the method of simple clamping to any shaft.

This can be achieved without prior machining of the shaft, eliminating clamping parts and assembly work.

A further advantage is the positioning of the lever arm to any required position.

The shaft tolerance should be within h11; to transmit higher torques the hub can be supplied with a keyway.

see also...

- *Gear Lever Handles GN 310 (Steel / Stainless Steel)* → Page 90

How to order (Steel)	1	d ₁
GN 150-28-B14	2	d ₂

How to order (Stainless steel)	1	d ₁
GN 150.5-32-B14	2	d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

