



2 Type

- A** For two-hole flange (d₁ = 60 / 90 / 113)
- B** For four-hole flange (d₁ = 113 / 126)

1 **1**

d ₁ Ø Leveling foot GN 148	l ₁ Type A	l ₂ Type B	d ₂ Type A	d ₃	m ₁ Type A	m ₂ Type B	s
60	128	-	78	65	110	-	3
90	170	-	110	90	140	-	3
113	216	168	150	120	184	132	4
126	-	184	-	150	-	150	4

Specification

- Rubber (NBR)
 - Hardness 68±5 Shore A
 - Black
 - Oil resistant
- *Elastomer Characteristics* → Page 2158
- RoHS

Information

Rubber pads GN 148.2 in connection with GN 148 leveling feet are used for setting up machines and units if no firm bolt connection to the ground is required.

To be fixed to the leveling foot, they are snapped into the attachment bore holes of the flanges. Small pimples at the bottom face of the rubber pads enhance the stability.

see also...

- *Leveling Feet GN 148* → Page 1492

How to order

GN 148.2-168-B

1 l₂ (l₁)

2 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

