



- 3** Type
- C** 2x2 bores for countersunk screws

1 l_1		2 l_2		d_1	d_2	h_1	h_2	h_3	h_4	h_5	l_3	l_4	$m_1 \pm 0,25$	$m_2 \pm 0,25$
Nominal dimension	Actual dimension	Nominal dimension	Actual dimension											
48	48	49	49,5	5,5	4	19	11	13	36	26	44	17	31	30
64	64	65	65	6,5	5	23	13,5	15	36	30	44	24	40	40
98	97,5	98	96,5	10,5	8	35	20,5	23	48	46	63	35	62,5	59,5

Specification

- Plastic (Polyamide PA)
 - Black, matte finish
 - Temperature resistant up to 80 °C
- Pin
 - Steel, blackened
- Safety hand levers GN 604.2
 - Plastic (Polyamide PA)
 - Black, matte finish
- *Load Rating Information* → Page 2126
- *Plastic Characteristics* → Page 2158
- **RoHS**

Information

With hinges GN 151.2, doors, flaps etc. can be locked in any position.

When not operated, this clamping lever is not connected to the thread of the hinge pin and it is in a „free-wheel“ position.

By pushing down the centre button of the lever it engages itself in two notches and the hinge can be tightened or loosened.

It prevents this hinge from being moved accidentally and in addition it ensures that this lever will never interfere with the movement of this lever.

see also...

- *List of Hinge Types* → Page 1284 ff.
- *Hinges GN 151 (not Adjustable)* → Page 1311

How to order

GN 151.2-64-65-C

- 1** l_1
- 2** l_2
- 3** Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

