



Type SH



Type EH



Bores for countersunk screw DIN 7991



Bores for socket cap screw DIN 912  
hex head screw ISO 4014



**4 Type**

- SH** 2x2 bores for countersunk screws
- EH** 2x2 bores for socket cap screws / hexagon screws

| 1     |                   | 2                |                   | 3                |       |       |       |       |       |            |       |       |                |                |     |  |
|-------|-------------------|------------------|-------------------|------------------|-------|-------|-------|-------|-------|------------|-------|-------|----------------|----------------|-----|--|
| $l_1$ | Nominal dimension | Actual dimension | Nominal dimension | Actual dimension | $d_1$ | $d_2$ | $h_1$ | $h_2$ | $h_3$ | $h_4 -0,5$ | $h_5$ | $l_3$ | $m_1 \pm 0,25$ | $m_2 \pm 0,25$ | A/F |  |
| 40    |                   | 38,5             | 40                | 39,5             | 4,5   | 3     | 13    | 9     | 4,5   | 4          | 18    | 16,5  | 25             | 25             | 7   |  |
| 49    |                   | 49               | 49                | 49,5             | 5,5   | 4     | 16,5  | 11,5  | 5     | 6          | 23    | 21    | 31             | 30,5           | 8   |  |
| 49    |                   | 49               | 49                | 49,5             | 6,5*  | 4     | 16,5  | 11,5  | -     | 6          | 23    | 21    | 31             | 30,5           | 10  |  |
| 65    |                   | 64               | 65                | 65               | 6,5   | 5     | 21,5  | 15    | 9     | 7,5        | 30    | 27,5  | 40             | 40             | 10  |  |

\* only available in type EH

**Specification**

- Plastic (Polyamide PA)
  - Black, matte finish
  - Temperature resistant up to 80 °C
- Pin  
Plastic (Polyacetal POM)
- *Load Rating Information* → Page 2126
- *Plastic Characteristics* → Page 2158
- RoHS

**Information**

- see also...
- *List of Hinge Types* → Page 1284 ff.

How to order

|   |       |
|---|-------|
| 1 | $l_1$ |
| 2 | $l_2$ |
| 3 | $d_1$ |
| 4 | Type  |

**GN 151.5-49-49-5,5-SH**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

