





Swivelling range



Type A



Type C



Type B

Bores for
hexagon screw
ISO 4014-M6



elesa
Original design CFJ.

3 Type

- A 2x2 threaded blind bores
- C 2x2 threaded studs
- B 2x2 bores for hexagon screws

1

2

l_1	l_2	d_1	d_2	h_1	h_2	l_3	l_4	$m_1 \pm 0,25$	$m_2 \pm 0,25$	A/F	t_1	t_2
70	50	M 6	6,2	19,5	10	17	23,5	46	30	10	8	6

Specification

- Plastic (Polyamide PA)
 - Black, matte finish
 - Temperature resistant up to 80 °C
- Pin
 - Stainless steel AISI 303
- Threaded bushings
 - Brass, nickel plated
- Threaded studs
 - Brass, nickel plated
- *Load Rating Information* → Page 2126
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Hinges GN 158 have a special feature in that they cannot be dismantled from the outside. The assembly is only possible from the inside. The pin is not accessible since it is fully integrated in the plastic material.

This configuration meets ultimate safety and security standards.

see also...

- *List of Hinge Types* → Page 1284 ff.

How to order

GN 158-70-50-A

1	l_1
2	l_2
3	Type