



2 Identification no.

3 With stainless steel grub screw DIN 913



d ₁ Bore	d ₂	k Clamping length	Length l	t	x ₁	x ₂	y ₁	y ₂	z Screw location
B 10	5,5	32	25	6	40	28	40	28	M6-6
B 12	5,5	32	25	6	40	28	40	28	M6-6
B 14	5,5	32	25	6	40	28	40	28	M6-6
B 15	5,5	32	25	6	40	28	40	28	M6-6
B 16	5,5	32	25	6	40	28	40	28	M6-6
B 18	5,5	32	25	6	40	28	40	28	M6-6

Specification

- Aluminum
 - Powder coated
Black, RAL 9005, textured finish **● SW**
 - Plain, matte shot-blasted **○ BL**
- Grub screw DIN 913
Stainless steel AISI 304
- Stainless Steel Characteristics* → Page 2166
- RoHS



Information

The clamping bore of base plate connector clamps GN 162.8 is not machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

At the screw location **z** a grub screw reduces the bore cross-section for clamping.

see also...

- Base Plate Mounting Clamps GN 473 → Page 1789
- Base Plate Mounting Clamps GN 175 (Plastic) → Page 1807
- Construction Tubes GN 990 → Page 1835
- Base Plate Linear Actuator Connectors GN 162.1 → Page 1963

How to order

GN 162.8-B14-3-SW

1	d ₁
2	Identification no.
3	Finish