



**2 Type**

- A Without seals
- B With seals

**3 Identification no.**

- 4 With stainless steel cap nut DIN 917



d <sub>1</sub> Bore	b	d <sub>2</sub>	d <sub>3</sub>	k Clamping length	l <sub>1</sub>	m	t	x <sub>1</sub>	x <sub>2</sub>	y <sub>1</sub>	y <sub>2</sub>	z Screw location	Accessory Recom. hand lever GN 911.3 for z l <sub>2</sub>
B 30	22	6,5	37	50	36	35	6,5	60	42	60	42	M 8	63 78
B 50	30	10,7	60	85	48,5	60	9	105	74	105	74	M 10	78 92

**Specification**

- Stainless steel AISI CF-8  
Matte shot-blasted
- Carriage bolt DIN 603  
Stainless steel
- Cap nuts DIN 917 / Washers  
Stainless steel
- Seals
  - Sealing disks  
Plastic (Polyacetal POM)
  - Spacer ring  
Silicon, 40 ... 60 Shore A
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**Accessory**

- Adjustable Hand Levers GN 911.3  
→ Page 1785

**Information**

The clamping bores of base plate connector clamps GN 163.5 are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw location **z** the carriage bolt and the cap nut reduce the bore cross-section for clamping. Type B is equipped with seals at the screw location.

For clamping without tools, the cap nut can be replaced by an adjustable hand lever GN 911.3 listed in the table as accessory.

see also...

- *Stainless Steel Construction Tubes GN 990* → Page 1835
- *Plate Connector Clamps GN 162 (Bore Ø B12 ... B20)* → Page 1730
- *Base Plate Connector Clamps GN 162.3 (Bore Ø B12 ... B20)*  
→ Page 1731

**How to order**

**GN 163.5-B30-B-4**

1	d <sub>1</sub>
2	Type
3	Identification no.