



- 4** Type (Base plate)
- C3** Polished, rubber vulcanized, black

d ₁	d ₂	1					2					
		3					4					
		Version S / SK					Version T / TK					
60	M 8	40	50	63	-	-	-	-	-	-	-	-
60	M 10	50	60	80	100	-	-	-	-	-	-	-
60	M 12	60	80	100	125	-	-	-	-	-	-	-
60	M 16	-	-	-	-	75	100	125	150	200	250	-
80	M 8	40	50	63	-	-	-	-	-	-	-	-
80	M 10	50	60	80	100	-	-	-	-	-	-	-
80	M 12	60	80	100	125	-	-	-	-	-	-	-
80	M 16	-	-	-	-	75	100	125	150	200	250	-
80	M 20	-	-	-	-	75	100	125	150	200	250	-
80	M 24	-	-	-	-	100	125	150	200	300	-	-
100	M 8	40	50	63	-	-	-	-	-	-	-	-
100	M 10	50	60	80	100	-	-	-	-	-	-	-
100	M 12	60	80	100	125	-	-	-	-	-	-	-
100	M 16	-	-	-	-	75	100	125	150	200	250	-
100	M 20	-	-	-	-	75	100	125	150	200	250	-
100	M 24	-	-	-	-	100	125	150	200	300	-	-
120	M 20	-	-	-	-	75	100	125	150	200	250	-
120	M 24	-	-	-	-	100	125	150	200	300	-	-

Versions of threaded stem



5
S Without nut
SK With nut



5
T Without nut
TK With nut

External hex at the bottom at d_2
 M 8, M 10, M 12

Wrench flat at the bottom at d_2
 M 16, M 20, M 24, M 30

d_1	d_2			h_1	h_2	s	A/F ₁	A/F ₂	w in °
60	M 8	M 10	M 12	31	-	2	17	-	32
60	M 16	-	-	-	37	2	-	12	32
80	M 8	M 10	M 12	33	-	2	17	-	26
80	M 16	-	-	-	39	2	-	12	26
80	M 20	-	-	-	39	2	-	15	26
80	M 24	-	-	-	41	2	-	19	26
100	M 8	M 10	M 12	35	-	2	17	-	22
100	M 16	-	-	-	41	2	-	12	22
100	M 20	-	-	-	41	2	-	15	22
100	M 24	-	-	-	43	2	-	19	22
120	M 20	-	-	-	43	2	-	15	20
120	M 24	-	-	-	46	2	-	19	20

Specification

- Base plate
Stainless steel AISI 316L
- Threaded stem
Stainless steel AISI 316L
- Hex nut ISO 4032
Stainless steel AISI 316
- Rubber pad
Acrylonitrile butadiene rubber (NBR)
- Black
- FDA compliant
- Hardness 85±5 Shore A
- Vulcanized
- Load Rating Information → Page XYZ
- Plastic Characteristics → Page XYZ
- Stainless Steel Characteristics → Page XYZ
- RoHS

On request

- Rubber pad available in various colors

Information

Leveling feet GN 18 are particularly suitable for use in aggressive environments.

The inclined surfaces for liquid runoff and the high surface quality of the base plate simplify cleaning and prevent the accumulation of dust or dirt. The FDA compliant and vulcanised rubber underlay seals the base against the resting surface and allows the feet to be used in food-processing areas or the pharmaceutical industry, for example.

The leveling feet are supplied assembled and cannot be disassembled.

see also...

- Leveling Feet GN 17 (Stainless Steel AISI 304) → Page XYZ
- Leveling Feet GN 19 (Stainless Steel, Hygienic Design) → Page XYZ
- Leveling Feet GN 44 (with / without Rubber Pad) → Page XYZ
- Leveling Feet GN 45 (with Mounting Flange) → Page XYZ

How to order

1	d_1
2	d_2
3	h_1
4	Type (Base plate)
5	Version (Stud)

GN 18-60-M10-100-C3-S

