




1 d min.	2 d max.	Length l	b
A 16	20	110	3
A 25	28	136	4
A 30	32	136	4
A 34	36	170	5
A 40	42	170	5
A 45	50	206	6
A 52	55	206	6
A 58	62	240	7
A 65	70	240	7
A 68	75	240	7
A 80	90	280	8
A 95	100	280	8

Specification

Steel
Blackened
RoHS

see also...	Page
DIN 70852 Slotted Locknuts	QVX
GN 1804.2 Slotted Locknuts	QVX
GN 1804.1 Slotted Locknuts	QVX
DIN 1804 Slotted Locknuts (Steel / Stainless Steel)	QVX
GN 350 Leveling Sets	QVX
GN 350.5 Leveling Sets	QVX
GN 350.1 Leveling Sets	QVX
GN 350.2 Leveling Sets	QVX
GN 360 Leveling Sets (Steel / Stainless Steel)	QVX

How to order	1 d min.
DIN 1810-A34-36	2 d max.