



3.1

3.2

3.3



d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	b	h	Code no. C-Spanner
M 12 x 1,5	28	23	M 4	5	6	DIN 1810-A25-28
M 14 x 1,5	30	25	M 4	5	7	DIN 1810-A30-32
M 16 x 1,5	32	27	M 5	5	7	DIN 1810-A30-32
M 18 x 1,5	34	28	M 5	6	8	DIN 1810-A34-36
M 20 x 1,5	36	30	M 5	6	8	DIN 1810-A34-36
M 22 x 1,5	40	34	M 5	6	9	DIN 1810-A40-42
M 24 x 1,5	42	36	M 5	6	9	DIN 1810-A40-42
M 30 x 1,5	50	43	M 5	7	10	DIN 1810-A45-50
M 35 x 1,5	55	48	M 6	7	11	DIN 1810-A52-55
M 40 x 1,5	62	54	M 8	8	12	DIN 1810-A58-62

3.4

3.5

3.6

### Specification

- Nut  
Steel  
- Property class 5  
- Blackened
- Set screw  
Steel, blackened
- Strength Values of Nuts → Page 2152
- RoHS

ST

### Accessory

- C-Spanner DIN 1810  
(Code no. see table)



### Information

Slotted locknuts GN 1804.2 with thread locking can be secured against twisting by twisting off the threaded shaft via a d<sub>4</sub> set screw. The thread flanks of the nut ensure damage-free securing and can be used as often as needed.

The d<sub>3</sub> offset plane surface is intended as an axial contact surface.

see also...

- Slotted Locknuts DIN 1804 (Steel / Stainless Steel) → Page 1074
- Slotted Locknuts GN 1804.1 (Self-locking) → Page 1076
- Slotted Locknuts DIN 70852 (Flat Design) → Page 1075

3.7

3.8

3.9

How to order

**GN 1804.2-M20x1,5-ST**

1 d<sub>1</sub>

2 Material

