



2

3

d <sub>1</sub>	d <sub>2</sub>	b	d <sub>3</sub> <sup>+0.2 +0.5</sup>	Length l	m	s	t	Countersunk screw DIN 7991	for cabinet U-handles
8	M 4	10	4	20	10	3	7	M 4 x 10	GN 425-8-...
10	M 5	12	5	24	12	4	8	M 5 x 12	GN 425-10-... / GN 425.1-10-...
12	M 6	15	6	30	15	4,5	9,5	M 6 x 14	GN 425-12-... / GN 425.1-12-...
16	M 6	18	6	34	16	4,5	9,5	M 6 x 14	GN 425-16-...
20	M 6	22	6	40	18	4,5	9,5	M 6 x 14	GN 565-20-... / GN 565.5-20-...
20	M 8	22	8	42	20	6	12	M 8 x 18	GN 426-20-... / GN 426.1-20-...
26	M 8	28	8	52	24	6	12	M 8 x 18	GN 565-26-...
28	M 10	30	10	56	26	6,5	13,5	M 10 x 20	GN 426-28-... / GN 426.1-28-...

Specification

Fastening plates

- Zinc die casting
- Powder coated
  - Black, RAL 9005, textured finish
  - Silver, RAL 9006, textured finish

ZD

- SW
- SR

Countersunk screws DIN 7991

- Steel
- Zinc plated, blue passivated

RoHS

Fastening sets GN 181 make it possible to mount different cabinet U-handles and tubular handles with internal thread from the operator's side. The mounting position of the fastening plates is freely customizable, allowing a sideways offset or mounting with different drillhole spacings. A fastening set consists of two fastening plates and two countersunk screws.

How to order

1 2 3 4  
**GN 181-ZD-28-M10-SW**

- 1 Material
- 2 d<sub>1</sub>
- 3 d<sub>2</sub>
- 4 Color

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

