



- 3 Identification no.
- 2 With 3 stainless steel socket cap screws DIN 912

<b>1</b> d <sub>1</sub> Bore	<b>2</b> d <sub>2</sub> Bore	d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	m	z Screw locations	Accessory Recom. hand lever GN 911 for z l <sub>4</sub>	
B 20	B 20	40	M 8	120	80	52	60	M8-25	-	-
B 25	B 25	40	M 8	120	80	52	60	M8-25	78	-
B 30	B 30	40	M 8	120	80	52	60	M8-25	63	78
B 40	B 40	65	M 10	206	135,5	77,5	103	M10-50	-	-
B 42	B 42	65	M 10	206	135,5	77,5	103	M10-50	-	-
B 45	B 45	65	M 10	206	135,5	77,5	103	M10-50	92	-
B 48	B 48	65	M 10	206	135,5	77,5	103	M10-50	78	92
B 50	B 50	65	M 10	206	135,5	77,5	103	M10-50	78	92

**Specification**

- Aluminum
  - Powder coated  
Black, RAL 9005, textured finish ● **SW**
  - Plain finish, matte shot-blasted ○ **BL**
- Socket cap screws DIN 912  
Stainless steel AISI 304
- Hex nuts DIN 985  
Stainless steel AISI 304  
Self-locking via polyamide ring
- Grub screws DIN 914  
Stainless steel AISI 304
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**Accessory**

- Adjustable Hand Levers GN 911  
→ Page 1784



**Information**

The clamping bores of angle connector clamps GN 198 are designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Angle Connector Clamps GN 196* → Page 1747

How to order	
<b>1</b>	d <sub>1</sub>
<b>2</b>	d <sub>2</sub>
<b>3</b>	Identification no.
<b>4</b>	Finish
<b>GN 198-B25-B25-2-SW</b>	