



Application example



d₁	Length l	d₂	d₃	A/F	t₁	t₂
M 12	56	25	25,8	19	15,5	50
M 16	62	28	28,8	22	20,5	55
M 20	68	32	32,8	27	25,5	60
M 24	74	36	36,8	30	30,5	65

Specification

- Cover sleeve
Stainless steel AISI 304
- Sealing ring
 - H-NBR **H**
Temperature resistant -25 °C to +150 °C
 - EPDM **E**
Temperature resistant -40 °C to +120 °C
 - Blue
 - Hardness 85 ±5 Shore A
 - FDA compliant
- [EHEDG and 3-A Principles → Page 1454](#)
- [Plastic Characteristics → Page 2158](#)
- [Stainless Steel Characteristics → Page 2166](#)
- RoHS

Accessory

- Sealing Rings GN 7600 → [Page 1596](#)

Information

Cover sleeves GN 20.1 comply with the guidelines of the EHEDG, the 3-A sanitary standard 88-01 and the DGUV testing principles, making them extremely suitable for use in hygienic areas.

These cover protruding male threads while also substituting for lock nuts. The sealed mounting surfaces enable fastening without dead spaces. The high quality finish prevents adherence of dirt and facilitates cleaning.

see also...

- Product Family [Hygienic Design](#) → [Page 16](#)
- Leveling Feet GN 20 (Stainless Steel, [Hygienic Design](#)) → [Page 1450 / 1452](#)
- Leveling Feet GN 19 (Stainless Steel, [Hygienic Design](#)) → [Page XYZ](#)

How to order

GN 20.1-M12-56-H

1	d₁
2	Length l
3	Material (Sealing ring)