


1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4



- 3 Type**
- E Angled lever
 - D Straight lever



1 2

d ₁	d ₂			d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈ Type E	Type D	h ₅ Stroke	l ₂ ≈ Type E	Type D	l ₃ ≈	t min.
21	M 6	M 8	-	13,5	8	20	33,5	31	1	59	36	4	75	80,5	70	11
24	M 8	M 10	-	16	10	25	40	37	2,5	75	43,5	4,5	101	108	96	14
28	M 10	M 12	-	19	12	30	48,5	44,5	4,5	89	52,5	4,5	116	124	110	17
33	M 12	M 14	M 16	23	12	32	55	51,5	6	100,5	60	5,5	131,5	140,5	124	22
40	M 16	M 20	-	28	14	35	68	64	6	118	71,5	5,5	148	158	138	36

Specification

Hub / Shaft

Steel, blackened

Insert

Steel, blackened

Ball knob DIN 319

Plastic, phenolic resin (PF)

Black, shiny finish

Safety circlip

Plastic, Polyacetal (POM)

RoHS

Adjustable tension levers GN 212.3 have proved to be ideal whenever parts have to be clamped in a confined space or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

	Page
GN 212.5 Adjustable Tension Levers (Insert Stainless Steel, with Internal Thread)	QVX
GN 312 Safety Tension Levers	QVX

Technical Information

Plastic Characteristics

Page

QVX

QVX

QVX

How to order

GN 212.3-28-M12-E

1	d ₁
2	d ₂
3	Type