


2 Bore code

- B** Without keyway
K With keyway DIN 6885-1 P9
V With square DIN 79

1 d_1	3 d_2 Bore H7 Square H11	d_3	d_4	h_1	h_2	$h_3 \approx$	Length $l \approx$
25	8	6	16	14	5	35	45
32	10	8	20	18	6,5	48	62
40	12	10	30	22	8,5	77	95
52	16	14	40	28	11	96	136

Specification
Hub / Shaft

Steel
 Blackened

Ball knobs DIN 319

Plastic, phenolic resin (PF)
 Black, shiny finish

RoHS

see also...

GN 210 Gear Levers (Zinc Die Casting)

GN 750 Control Levers (Steel)

Page

QVX

QVX

Technical Information

Keyways DIN 6885-1

Squares DIN 79

ISO Fundamental Tolerances

QVX

QVX

QVX

How to order

GN 223-32-B10

1	d_1
2	Bore code
3	d_2