



ROSTFREI
Inox
Stainless
Steel

3 Type

E Angled lever

1

2

d ₁	d ₂	d ₃	d ₄	d ₅	h ₁	h ₃	h ₄ ≈	h ₅ Stroke	l ₂ ≈	l ₃ ≈	t min.
21	M 6 M 8	13,5	8	20	33,5	1	59	4	75	70	11
24	M 8 M 10	16	10	25	40	2,5	75	4,5	101	96	14
28	M 10 M 12	19	12	30	48,5	4,5	89	4,5	116	110	17

Specification

- Stainless steel AISI 303
Matte shot-blasted
- Ball knobs DIN 319
Plastic, Duroplast
Black, shiny finish
- Safety circlip
Plastic (Polyacetal POM)
- Plastic Characteristics* → Page 2158
- Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- Straight lever (90°)
- With inch threads

Information

Adjustable tension levers GN 212.5 have proved to be ideal whenever parts have to be clamped in a confined space or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

- Adjustable Tension Levers GN 212.3 (Steel, Blackened)* → Page 480

How to order

GN 212.5-24-M10-E

1	d ₁
2	d ₂
4	Type