



1

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h	Length l ±0,25	t min.
18	M 6	12	42	100	12
20	M 8	14	47	112	15
22	M 10	16	53	125	18
25	M 12	18	59	140	20

**Specification**

**Cast iron (GS45)**

- Powder coated
- Black, RAL 9005, textured finish
- Plain finish, tumbled
- Unfinished casting, fettled
- Contact surface machined

- SW
- BL

RoHS

2

The shape, fastening thread and material all make GN 225 cabinet U-handles highly stable.

**see also...**

GN 425 Cabinet U-Handles (Steel)

Page

QVX

**Technical Information**

Load Rating Information

QVX

**How to order**

**GN 225-20-SW**

1 d<sub>1</sub>

2 Finish

