



1.1

1.2

1.3

1.4

2.1

2.2

2.3

2.4



2

3

d	Square	s ₁ ±0,1	s ₂ ±0,1	l ₁ ±0,5	l ₂	No. of spokes
	s ₀					
50	V 6	5,9	6,15	8,5	12	3
50	V 7	6,9	7,15	8,5	12	3
60	V 6	5,9	6,15	8,5	12	3
60	V 7	6,9	7,15	8,5	12	3
70	V 7	6,9	7,15	10	15	3
70	V 8	7,9	8,15	10	15	3
80	V 8	7,9	8,15	11	16	3
80	V 9	8,9	9,15	11	16	3
90	V 9	8,9	9,15	11	16	3
100	V 9	8,9	9,15	13	20	3
100	V 10	9,9	10,15	13	20	3
130	V 12	11,9	12,15	15	23	3

Specification

1

4

- Pressed steel **ST**
- Powder coated
 - Black, RAL 9005, matte finish **● SW**
 - Red, RAL 3000, matte finish **● RT**
 - Zinc plated, blue passivated **ZB**
- RoHS

Information

Pressed steel handwheels GN 227.6 have been specially developed for valves and consist of a **single** unwelded piece of pressed sheet metal manufactured by a special process.

They offer high mechanical strength and are not affected by shocks and knocks.

How to order

GN 227.6-ST-60-V7-SW

1	Material
2	d
3	s ₀
4	Finish