

STAINLESS ★★★★

4 Type (Base plate)

D0 Fine turned, without rubber underlay

D1 Fine turned, with rubber underlay, inlaid, black

1 d_1	2 d_2	3 l_1 Version S / SK				Version T / TK						k
80	M 8	40	50	63	-	-	-	-	-	-	-	54
80	M 10	50	60	80	100	-	-	-	-	-	-	54
80	M 12	60	80	100	125	-	-	-	-	-	-	54
80	M 16	-	-	-	-	75	100	125	150	200	250	54
80	M 20	-	-	-	-	75	100	125	150	200	250	54
80	M 24	-	-	-	-	100	125	150	200	300	-	54
100	M 8	40	50	63	-	-	-	-	-	-	-	70
100	M 10	50	60	80	100	-	-	-	-	-	-	70
100	M 12	60	80	100	125	-	-	-	-	-	-	70
100	M 16	-	-	-	-	75	100	125	150	200	250	70
100	M 20	-	-	-	-	75	100	125	150	200	250	70
100	M 24	-	-	-	-	100	125	150	200	300	-	70
120	M 20	-	-	-	-	75	100	125	150	200	250	95,5
120	M 24	-	-	-	-	100	125	150	200	300	-	95,5

Specification

Base plate
Stainless steel AISI 316L

Threaded stem
Stainless steel AISI 316L

Hex nuts ISO 4032
Stainless steel

Mounting screw
Stainless steel

Rubber underlay
Acrylonitrile butadiene rubber (NBR)
- Inlaid
- Black
- Hardness 70 Shore A

RoHS

Technical Information	Page
Load Rating	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Leveling feet GN 22 / GN 24 are particularly suitable for use in aggressive environments.
The leveling feet are supplied assembled and cannot be disassembled.

see also...	Page
GN 18 Leveling Feet (Stainless Steel, FDA compliant)	QVX
GN 21 | **GN 23** Leveling Feet (Stainless Steel, Turned Base Plate)	QVX
GN 44 Leveling Feet (Stainless Steel, Flat Base Plate)	QVX

How to order (without mounting holes)

1 2 3 4 5
GN 22-100-M20-75-D1-TK

1	d_1
2	d_2
3	l_1
4	Type (Base plate)
5	Version (Threaded stem)

How to order (with mounting holes)

1 2 3 4 5
GN 24-80-M10-50-D0-S

1	d_1
2	d_2
3	l_1
4	Type (Base plate)
5	Version (Threaded stem)

Versions of threaded stem



5
S Without nut
SK With nut

External hex at the bottom at d_2
M 8, M 10, M 12



5
T Without nut
TK With nut

Wrench flat at the bottom d_2
M 16, M 20, M 24, M 30

d_1	d_2	h_1	h_2	h_3	h_4	A/F_1	A/F_2
80	M 8	8,5	2	19,5	-	17	-
80	M 10	8,5	2	19,5	-	17	-
80	M 12	8,5	2	19,5	-	17	-
80	M 16	8,5	2	-	25,5	-	12
80	M 20	8,5	2	-	27	-	15
80	M 24	8,5	2	-	30,5	-	19
100	M 8	9	3	20,5	-	17	-
100	M 10	9	3	20,5	-	17	-
100	M 12	9	3	20,5	-	17	-
100	M 16	9	3	-	26,5	-	12
100	M 20	9	3	-	28	-	15
100	M 24	9	3	-	31,5	-	19
120	M 20	12	3,5	-	32	-	15
120	M 24	12	3,5	-	35,5	-	19