



1

2

d <sub>1</sub>	Square (conical)		d <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub> ±1	No. of spokes	Thickness of pressed steel
	s <sub>1</sub>	s <sub>2</sub>					
125	VK 11	12,7	28	17	31	3	1,2
150	VK 12	13,8	30	18	33,5	3	1,5
200	VK 14	16	35	20	40,5	3	2
250	VK 17	19,25	36	23	47	4	2
300	VK 19	21,8	42	28	59	5	2
400	VK 24	27	48	30	66	5	2,5

**Specification**

3

- Pressed steel  
Bathodic dip coated (KTL)  
Black, RAL 9005  
Red, RAL 3000



- Hub  
Steel, welded

• RoHS

**On request**

- With bore B
- With square V
- Neutral, no labeling

**Information**

Pressed steel handwheels GN 227.7 feature high mechanical strength and a coating for increased corrosion resistance. They are also not affected by shock and knocks.

The conical square hole allows easy installation and firm seating on a spindle. The cast shape prevents injuries from sharp edges during handling. The engraved labels “SHUT” and “OPEN” help with safe and correct operation of the valves.

see also...

- *Countersunk Washers GN 184* → Page 1090
- *Pressed Steel Handwheels GN 227.6* → Page 285

**How to order**

**GN 227.7-200-VK14-SWK**

1	d <sub>1</sub>
2	s <sub>1</sub>
3	Color