




$d_1 = 14...30$




Coupling spider






2 Bore code

- B** Without keyway
- K** With keyway (from $d_1 = 30$)


$d_1 = 40$



$d_1 = 55$



Assembly instruction



1

3

d_1	$d_2 - d_3$ H8 Recommended shaft tolerance h7									
14	3-3	3-4	3-5	3-6	4-4	4-5	4-6	5-5	5-6	6-6
20	5-5	5-6	5-8	6-6	6-8	8-8	-	-	-	-
30	8-8	8-10	8-12	8-14	10-10	10-12	10-14	12-12	12-14	14-14
40	12-12	12-14	12-15	12-16	14-14	14-15	14-16	15-15	15-16	16-16
55	18-18	18-19	18-20	18-25	19-19	19-20	19-25	20-20	20-25	25-25

d_1	d_4	l_1	l_2 Recommended shaft insertion depth	l_3	l_4	s Recommended installation spacing
14	M 2 / M 1,6*	22	7	3,5	4 / 5*	1
20	M 2,5	30	10	5	6,5	1
30	M 4 / M 3**	35	11	5,5	10 / 11**	1,5
40	M 5	66	25	8,5	14	2
55	M 6	78	30	10,5	20	2

* for bore $d_2 / d_3 = 6$ ** for bore $d_2 / d_3 = 14$

d ₁	Coupling spider	Shore hardness coupling spider	Rated torque in Nm	Max. torque in Nm	Max. speed (min ⁻¹)	Moment of inertia in kgm ²	Static torsional stiffness in Nm/rad	Max. shaft misalignment		
								Lateral in mm	Axial in mm	Angular in °
14	BS	80A	0,7	1,4	45.000	2,0 x 10 ⁻⁷	8	0,15	0,6	1
	WS	92A	1,2	2,4	45.000	2,0 x 10 ⁻⁷	14	0,1	0,6	1
	RS	98A	2	4	45.000	2,0 x 10 ⁻⁷	22	0,1	0,6	1
20	BS	80A	1,8	3,6	31.000	1,1 x 10 ⁻⁶	16	0,2	0,8	1
	WS	92A	3	6	31.000	1,1 x 10 ⁻⁶	29	0,15	0,8	1
	RS	98A	5	10	31.000	1,1 x 10 ⁻⁶	55	0,1	0,8	1
30	BS	80A	4	8	21.000	6,2 x 10 ⁻⁶	46	0,2	1	1
	WS	92A	7,5	15	21.000	6,2 x 10 ⁻⁶	73	0,15	1	1
	RS	98A	12,5	25	21.000	6,2 x 10 ⁻⁶	130	0,1	1	1
40	BS	80A	4,9	9,8	15.000	3,7 x 10 ⁻⁵	380	0,15	1,2	1
	WS	92A	10	20	15.000	3,7 x 10 ⁻⁵	570	0,1	1,2	1
	RS	98A	17	34	15.000	3,7 x 10 ⁻⁵	1200	0,1	1,2	1
55	BS	80A	17	34	11.000	1,6 x 10 ⁻⁴	1400	0,2	1,4	1
	WS	92A	35	70	11.000	1,6 x 10 ⁻⁴	1600	0,15	1,4	1
	RS	98A	60	120	11.000	1,6 x 10 ⁻⁴	2600	0,1	1,4	1

Specification



- Hub
Aluminum **AL**
Anodized, natural color
- Coupling spider
Thermoplastic polyurethane (TPU)
- Temperature resistant up to 60 °C
- Hardness
80 Shore A, blue **BS**
92 Shore A, white **WS**
98 Shore A, red **RS**
- Socket cap screws DIN 912
Steel, blackened
- Temperature range: -20 °C up to +60 °C
- Keyway P9 DIN 6885 → Page 2078
- ISO Fundamental Tolerances → Page 2151
- Elastomer Characteristics → Page 2158
- RoHS

Accessory

- Coupling Spiders GN 2240.1 → Page 1692

Information

Elastomer jaw couplings GN 2240 can transmit very high torques while compensating for shaft misalignments and runout tolerances. They are preferred in applications where the focus lies on pure torque and power transmission.

The choice of three coupling spiders with different hardness values allows the properties of the coupling to be optimally matched to the specific requirements. The clamping hubs and simple plug-in installation make jaw couplings very easy to assemble.

With the bore code K, the keyway is always integrated into both bores d₂ and d₃.

see also...

- *Assembly Instructions on Couplings* → Page 1694
- *Technical Information on Couplings* → Page 1696
- *Elastomer Jaw Couplings GN 2241 (with Grub Screw)* → Page 1682
- *Oldham Couplings GN 2242 (with Clamping Hub)* → Page 1684

How to order

1	d ₁
2	Bore code
3	d ₂ - d ₃
4	Material
5	Hardness



GN 2240-40-B12-16-AL-RS

