



2

l_1	b	d	h_1	h_2	l_2	m
57	12	4,5	13	1	37	45

Specification

1

3

- Housing brass
 - Powder coated, textured finish
 - Black, RAL 9005
 - Silver, RAL 9006
- Spirit level element
 - Glass plastic body
 - Filling
 - Green-transparent
- Casting compound
 - Mineral-based

RoHS

MSW

MSR

G

On request

- Filling, colorless-transparent
- Other sensitivities
- Other colors

Information

Screw-on spirit levels GN 2282 are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

The spirit levels are aligned in relation to the finished reference surface so that the bubble is centered in the middle of the marking lines once the horizontal position of the contact surface in the longitudinal direction is reached.

see also...

- General Information on Bull's Eye, Screw-On and Cross Spirit Levels → Page 315
- Screw-On Spirit Levels GN 2283 (for Mounting with Screws) → Page 324
- Cross Spirit Levels GN 2276 (for Mounting with Screws) → Page 325
- Bull's Eye Spirit Levels GN 2280 (Adjustable) → Page 321

How to order

1	Material / Finish
2	l_1
3	Filling
4	Sensitivity
5	Identification no.

GN 2282-MSR-57-G-50-3