



elesa
Original design RE.E3

2 Bearing type

G Friction bearing

3 Type

A Wheel without bracket

1

d ₁ Wheel Ø	b ₁	b ₂	d ₂	Recommended ergonomic max. load in N	Max. static load capacity in N	Max. dynamic load capacity in N
80	25	39	12	500	2600	650
100	30	44	12	750	3000	800
125	37,5	44	15	850	3300	1300
150	40	44	15	1000	3500	1700
200	50	58	20	1400	4100	2300

Specification

Wheel tread

- Rubber
- Vulcanized
 - Black
 - Hardness 80 Shore A

Wheel core

Steel sheet metal, zinc plated

Operating temperature -20 °C to +60 °C

RoHS

Wheels GN 22874 are used in industrial and public indoor and outdoor areas for moving transport carts, for example.

The wheel tread is suitable for all floor types. It is gentle on floors and good at overcoming obstacles. Tread wear may occur on rough floors.

see also...	Page
GN 22874 Medium Duty Casters (with Bracket, Light Version)	QVX
GN 22872 Wheels (Wheel Tread Thermoplastic Elastomer)	QVX
GN 22873 Wheels (Wheel Tread Rubber, Wheel Core Polypropylene)	QVX
GN 22875 Wheels (Wheel Tread Rubber, Wheel Core Aluminum)	QVX

Technical Information

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX

How to order	1 d ₁
GN 22874-100-G-A	2 Bearing type
	3 Type