



elesa

Original design RE.E3

**2 Bearing type**

G Friction bearing

**3 Type**

A Wheel without bracket

1

d <sub>1</sub> Wheel Ø	b <sub>1</sub>	b <sub>2</sub>	d <sub>2</sub>	Recommended ergonomic max. load in N	Max. static load capacity in N	Max. dynamic load capacity in N
80	25	39	12	500	2600	650
100	30	44	12	750	3000	800
125	37,5	44	15	850	3300	1300
150	40	44	15	1000	3500	1700
200	50	58	20	1400	4100	2300

**Specification****Wheel tread**

Rubber

- Vulcanized, black
- Hardness 80 Shore A

**Wheel core**

Steel sheet metal, zinc plated

**Operating temperature** -20 °C to +60 °C

RoHS

Wheels GN 22874 are used in industrial and public indoor and outdoor areas for moving transport carts, for example.

The wheel tread is suitable for all floor types. It is gentle on floors and good at overcoming obstacles. Tread wear may occur on rough floors.

**see also...**

	Page
<b>GN 22874</b> Medium Duty Casters (with Bracket, Light Version)	QVX
<b>GN 22872</b> Wheels (Wheel Tread Thermoplastic Elastomer)	QVX
<b>GN 22873</b> Wheels (Wheel Tread Rubber, Wheel Core Polypropylene)	QVX
<b>GN 22875</b> Wheels (Wheel Tread Rubber, Wheel Core Aluminum)	QVX

**Technical Information**

Operating Conditions of Wheels and Casters	QVX
--	-----

Technical Information for Wheels and Casters	QVX
--	-----

**How to order****GN 22874-100-G-A**

1	d <sub>1</sub>
2	Bearing type
3	Type