



elesa
Original design RE.G1

2 Bearing type

G Friction bearing

3 Type

A Wheel without bracket

1

d ₁ Wheel Ø	b ₁	b ₂	d ₂	Recommended ergonomic max. load in N	Max. static load capacity in N	Max. dynamic load capacity in N
80	30	39	12	700	1000	700
100	30	44	12	1000	1500	1000
125	35	44	15	1200	1800	1200
150	45	59	20	1800	2700	1800

Specification

Wheel tread

- Thermoplastic elastomer (TPE)
- Gray
 - Abrasion-resistant
 - Hardness 85 Shore A

Wheel core

Plastic, polypropylene (PP)

Operating temperature -20 °C to +70 °C

RoHS

Wheels GN 22872 are used in industrial and public indoor areas for moving transport carts, for example.

The wheel tread offers low rolling resistance and high elasticity. It is characterized by quiet running, is gentle on floors and leaves no marks.

see also...

	Page
GN 22872 Medium Duty Casters (with Bracket, Light Version)	QVX
GN 22873 Wheels (Wheel Tread Rubber)	QVX
GN 22874 Wheels (Wheel Tread Rubber, Wheel Core Steel Sheet Metal)	QVX
GN 22875 Wheels (Wheel Tread Rubber, Wheel Core Aluminum)	QVX

Technical Information

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

How to order	1 d ₁
GN 22872-100-G-A	2 Bearing type
	3 Type