



**elesa**  
Original design RE.C6-G

- 2 Bearing type**
  - G** Friction bearing
- 3 Type (bracket)**
  - L** Swivel bracket with mounting plate
  - LF** Swivel bracket with mounting plate, with total lock brake
  - R** Swivel bracket with center hole
  - RF** Swivel bracket with center hole, with total lock brake
  - G** Swivel bracket with threaded stud
  - GF** Swivel bracket with threaded stud, with total lock brake
- 4 Coding**
  - D** Double wheel version

$d_1$ Wheel Ø	$b$	$d_2$	$d_3$	$d_4$	$d_5$	Type R / RF	Type G / GF	$h$	$l_1$	$l_2$	$l_3$	$l_4$	$m_1$	$m_2$	$r$	Max. dynamic load capacity in N
50	18	6	M 10	10	55	52	70	60	60	25,5	25	38,5	48	83	1400	

**Specification**

**Wheel tread**

- Thermoplastic polyurethane (TPU)
- Injection molded
- Red
- Hardness 55 Shore D

**Wheel core**

Plastic, polyamide (PA)

**Bracket**

Steel sheet metal, zinc plated

**ST**

**Swivel head bracket**

Dual grease-lubricated ball bearing

**Operating temperature** -5 °C to +40 °C

RoHS

**Technical Information**

**Page**

Usage Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

Light duty casters GN 22880 are used in industrial and public areas for moving heavier materials and equipment, for example.

The wheel tread offers low rolling resistance and high elasticity as well as good wear and tearing resistance. It is good at overcoming obstacles. The double wheel design reduces the contact pressure and thus protects the running surface.

**see also...**

	Page
<b>GN 22880</b> Wheels (without Bracket)	QVX
<b>GN 22880</b> Light Duty Casters (Light Version)	QVX
<b>GN 22870</b> Light Duty Casters (Wheel Tread Rubber, Wheel Core Polypropylene)	QVX
<b>GN 22882</b> Medium Duty Casters (Wheel Tread Polyurethane, Orange)	QVX
<b>GN 22884</b> Medium Duty Casters (Wheel Tread Polyurethane, Blue)	QVX

**How to order**

<b>1</b>	$d_1$
<b>2</b>	Bearing type
<b>3</b>	Type (bracket)
<b>4</b>	Coding
<b>5</b>	Material (bracket)

**GN 22880-50-G-GF-D-ST**