



**elisa**  
Original design RE.E2

**2 Bearing type**

**G** Friction bearing

**3 Type**

**A** Wheel without bracket

<b>1</b> d <sub>1</sub> Wheel Ø	b	b <sub>2</sub>	d <sub>2</sub>	Recommended ergonomic max. load in N	Max. static load capacity in N	Max. dynamic load capacity in N
80	25	39	12	500	1500	650
100	30	44	12	750	2000	800
125	37,5	44	15	850	2250	1100
150	40	44	15	1000	2750	1300
180	45	59	20	1300	3500	1800
200	50	59	20	1400	4000	2250

**Specification**

**Wheel tread**

- Rubber
- Vulcanized
  - Black
  - Hardness 80 Shore A

**Wheel core**

Plastic, polypropylene (PP)

**Operating temperature** -20 °C to +60 °C

RoHS

Wheels GN 22873 are used in industrial and public indoor and outdoor areas for moving transport carts, for example.

The wheel tread is suitable for all floor types. It is gentle on floors and good at overcoming obstacles. Tread wear may occur on rough floors.

see also...	Page
<b>GN 22873</b> Medium Duty Casters (with Bracket, Light Version)	QVX
<b>GN 22872</b> Wheels (Wheel Tread Thermoplastic Elastomer)	QVX
<b>GN 22874</b> Wheels (Wheel Tread Rubber, Wheel Core Steel Sheet Metal)	QVX
<b>GN 22875</b> Wheels (Wheel Tread Rubber, Wheel Core Aluminum)	QVX

**Technical Information**

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

How to order	<b>1</b> d <sub>1</sub>
<b>GN 22873-180-G-A</b>	<b>2</b> Bearing type
	<b>3</b> Type