



elesa
Original design RE.E2-N.

- 2 Bearing type**
G Friction bearing
- 3 Type (bracket)**
B Rigid bracket
L Swivel bracket with mounting plate
LF Swivel bracket with mounting plate, with total lock brake
R Swivel bracket with center hole
RF Swivel bracket with center hole, with total lock brake
- 4 Coding**
L Light version

d ₁ Wheel Ø	b	d ₂	d ₃	d ₄	h	l ₁	l ₂	l ₃	m ₁	m ₂	m ₃	m ₄	r	Max. dynamic load capacity in N		
					Type B / L / LF Type R / RF		Type B Type L / LF			Type B Type L / LF						
80	25	9	12	73	107	100	85	85	40	45	60	60	75	80	120	650
100	30	9	12	73	128	128	85	85	35	45	60	60	75	80	120	800
125	37,5	9	12	73	156	156	85	85	37	45	60	60	75	80	120	1100
150	40	9	12	73	182	182	85	85	34	45	60	60	75	80	120	1300
180	45	11	20	102	219	214	114	110	56	73	85	87	105	105	156	1800
200	50	11	20	102	240	236	114	110	56	73	85	87	105	105	156	2250

Specification

Wheel tread

- Rubber
- Vulcanized, black
- Hardness 80 Shore A

Wheel core

Plastic, polypropylene (PP)

Bracket

Steel sheet metal, zinc plated

ST

Swivel head bracket

- Dual grease-lubricated ball bearing
- Dust protection ring on type L / LF
- Plastic, polyethylene (PE)

Operating temperature -20 °C to +60 °C

RoHS

Technical Information

Page

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

Medium duty casters GN 22873 are used in industrial and public indoor and outdoor areas for moving lightweight carts, for example. The wheel tread is suitable for all floor types. It is gentle on floors and good at overcoming obstacles. Tread wear may occur on rough floors.

see also...

GN 22873 Wheels (without Bracket)	Page QVX
GN 22872 Medium Duty Casters (Wheel Tread Thermoplastic Elastomer)	QVX
GN 22874 Medium Duty Casters (Wheel Tread Rubber, Wheel Core Steel Sheet Metal)	QVX
GN 22875 Medium Duty Casters (Wheel Tread Rubber, Wheel Core Aluminum)	QVX

How to order

1	d ₁
2	Bearing type
3	Type (bracket)
4	Coding
5	Material (bracket)

GN 22873-200-G-RF-L-ST