



**elesa**  
Original design RE.F1

**2 Bearing type**

**G** Friction bearing

**3 Type**

**A** Wheel without bracket

**1**

d <sub>1</sub> Wheel Ø	b <sub>1</sub>	b <sub>2</sub>	d <sub>2</sub>	Recommended ergonomic maximum load in N	Max. static load capacity in N	Max. dynamic load capacity in N
80	30	39	12	750	1600	750
100	30	44	12	1200	2000	1200
125	35	44	15	1800	3500	1800
150	45	59	20	2400	4500	2500
200	50	59	20	3000	5000	3000

**Specification**

**Wheel tread**

- Thermoplastic polyurethane (TPU)
- Injection molded
- Blue
- Hardness 85 Shore A

**Wheel core**

Plastic, polyamide (PA)

**Operating temperature** -15 °C to +70 °C

RoHS

Wheels GN 22884 are used in industrial and public indoor areas for moving transport carts, for example.

The wheel tread offers low rolling resistance and high elasticity as well as good wear and tearing resistance. It is good at overcoming obstacles.

**see also...**

	Page
<b>GN 22884</b> Medium Duty Casters (with Bracket, Light Version)	QVX
<b>GN 22880</b> Wheels (Wheel Tread Polyurethane, Red)	QVX
<b>GN 22882</b> Wheels (Wheel Tread Polyurethane, Orange)	QVX

**Technical Information**

Usage Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

**How to order**

**GN 22884-150-G-A**

<b>1</b>	d <sub>1</sub>
<b>2</b>	Bearing type
<b>3</b>	Type