



elesa
Original design RE.E3-N.

- 2 Bearing type**
- G Friction bearing
- 3 Type (bracket)**
- B Rigid bracket
- L Swivel bracket with mounting plate
- LF Swivel bracket with mounting plate, with total lock brake
- R Swivel bracket with center hole
- RF Swivel bracket with center hole, with total lock brake
- 4 Coding**
- L Light version

d ₁ Wheel Ø	b	d ₂	d ₃	d ₄	h	Type		l ₁	l ₂		l ₃	m ₁	m ₂		m ₃	m ₄	r	Max. dynamic load capacity in N
						B / L / LF	R / RF		Type B	Type L / LF			Type B	Type L / LF				
80	25	9	12	73	107	107		100	85	85	40	45	60	60	75	80	120	650
100	30	9	12	73	128	128		100	85	85	35	45	60	60	75	80	120	800
125	37,5	9	12	73	156	156		100	85	85	37	45	60	60	75	80	120	1300
150	40	9	12	73	182	182		100	85	85	34	45	60	60	75	80	120	1700
200	45	11	20	102	240	236		140	114	110	56	73	85	87	105	105	156	2300

Specification

Wheel tread

- Rubber
- Vulcanized, black
- Hardness 80 Shore A

Wheel core

Steel sheet metal, zinc plated

Bracket

Steel sheet metal, zinc plated

ST

Swivel head bracket

- Dual grease-lubricated ball bearing
- Dust protection ring on type L / LF
- Plastic, polyethylene (PE)

Operating temperature -20 °C to +60 °C

RoHS

Technical Information

Page

Operating Conditions of Wheels and Casters QVX

Technical Information for Wheels and Casters QVX

Medium duty casters GN 22874 are used in industrial and public indoor and outdoor areas for moving lightweight carts, for example.

The wheel tread is suitable for all floor types. It is gentle on floors and good at overcoming obstacles. Tread wear may occur on rough floors.

see also...

	Page
GN 22874 Wheels (without Bracket)	QVX
GN 22872 Medium Duty Casters (Wheel Tread Thermoplastic Elastomer)	QVX
GN 22873 Medium Duty Casters (Wheel Tread Rubber, Wheel Core Polypropylene)	QVX
GN 22875 Medium Duty Casters (Wheel Tread Rubber, Wheel Core Aluminum)	QVX

How to order

1	d ₁
2	Bearing type
3	Type (bracket)
4	Coding
5	Material (bracket)

GN 22874-100-G-L-L-ST

