



elesa

Original design RE.F5-N / -N-ESD



2 Bearing

K Ball bearing

3 Type (bracket)

B Rigid bracket

L Swivel bracket with mounting plate


LF Swivel bracket with mounting plate, with total lock brake

R Swivel bracket with center hole

RF Swivel bracket with center hole, with total lock brake

4 Coding

L Light version



1

d ₁ Wheel Ø	b	d ₂	d ₃	d ₄	h	Type		l ₁	l ₂		l ₃	m ₁	m ₂	m ₃	m ₄	r	Max. dynamic load capacity in N	
						Type B / L / LF	Type R / RF		Type B	Type L / LF							ST	STE
80	25	9	12	73	107	107	100	85	85	40	45	60	60	75	80	120	2000	1700
100	30	9	12	73	128	128	100	85	85	35	45	60	60	75	80	120	2000	2000
125	35	9	12	73	156	156	100	85	85	37	45	60	60	75	80	120	2200	2200
150	40	11	20	102	194	188	140	114	110	56	73	85	87	105	105	156	3000	3000
200	50	11	20	102	240	236	140	114	110	56	73	85	87	105	105	156	3000	3000

Specification

5

Wheel tread

- Plastic, polyurethane (PUR) at ST
 - Cast, yellow
 - Hardness 92 Shore A
- Plastic, polyurethane (PUR) at STE
 - Electrically conductive (antistatic)
 - Electrical resistance < 10⁹ Ω
 - Cast, dark grey
 - Wear resistant
 - Hardness 90 Shore A

Wheel core

Aluminum die casting

Bracket

- Steel sheet metal, zinc plated **ST**
- Steel sheet metal, zinc plated, ESD **STE**

Swivel head bracket

- Dual grease-lubricated ball bearing
- Dust protection ring on type L / LF
 - Plastic, polyethylene (PE)

Operating temperature -20 °C to +80 °C

RoHS

Medium duty casters GN 22885 are used in industrial and public indoor areas for moving lightweight carts, for example.

The wheel tread offers low rolling resistance and high elasticity as well as good wear and tearing resistance.

The ESD version has antistatic properties and therefore meets the requirements of ISO 22878:2004.

The low wear on the ball bearing increases the service life, and the mounting to the inner ring can be accomplished with zero axial backlash.

see also...

	Page
GN 22885 Wheels (without Bracket)	QVX
GN 22885 Medium Duty Casters (Medium Version)	QVX

Technical Information

Usage Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX

How to order

1	d ₁
2	Bearing type
3	Type (bracket)
4	Coding
5	Material (bracket)

GN 22885-125-K-RF-L-ST

1 2 3 4 5