



**elesa**  
Original design RE.G2

**2 Bearing type**

**K** Ball bearing

**3 Type (bracket)**

- B** Rigid bracket
- L** Swivel bracket with mounting plate
- LF** Swivel bracket with mounting plate, with total lock brake

**4 Coding**

**M** Medium version

**1**

d <sub>1</sub> Wheel Ø	b	d <sub>2</sub>	h	l <sub>1</sub>	l <sub>2</sub> Type B Type L / LF	l <sub>3</sub>	m <sub>1</sub>	m <sub>2</sub> Type B Type L / LF	m <sub>3</sub>	r	Max. dynamic load capacity in N
100*	40	9	138	100	85 85	46	60	- -	80	-	1800
125*	50	11	170	140	115 110	70	73	85 87	105	-	2300
160	50	11	205	140	115 110	70	73	85 87	105	126	3000
200	50	11	250	140	115 110	70	73	85 87	105	126	5000

\* Only available in type B and type L

**Specification**

**Wheel tread**

- Natural rubber (NR)
- Black
- Hardness 70 Shore A

**Wheel core**

Aluminum die casting

**Bracket**

Steel sheet, zinc plated **ST**

**Swivel head bracket**

- Dual grease-lubricated ball bearing
- Dust protection ring on type L / LF
- Plastic, polyethylene (PE)

**Operating temperature** -20 °C to +70 °C

RoHS

**Technical Information** Page

Operating Conditions of Wheels and Casters QVX

Technical Information for Wheels and Casters QVX

Plastic Characteristics QVX

Medium duty casters GN 22875 are used in industrial and public indoor and outdoor areas for moving medium weight carts, for example.

The wheel tread is suitable for all floor types. It runs quietly and is gentle on floors while offering good obstacle clearing and vibration damping.

The low wear on the ball bearing increases the service life, and the mounting to the inner ring can be accomplished with zero axial backlash.

**see also...**

**GN 22875** Wheels (without Bracket) Page QVX

**GN 22872** Medium Duty Casters (Wheel Tread Thermoplastic Elastomer) QVX

**GN 22873** Medium Duty Casters (Wheel Tread Rubber, Wheel Core Polypropylene) QVX

**GN 22874** Medium Duty Casters (Wheel Tread Rubber, Wheel Core Steel Sheet Metal) QVX

**How to order**

<b>1</b>	d <sub>1</sub>
<b>2</b>	Bearing type
<b>3</b>	Type (bracket)
<b>4</b>	Coding
<b>5</b>	Material (bracket)

**GN 22875-160-K-LF-M-ST**