



 **elesa**  
Original design RE.F8-H

**2 Bearing type**

**G** Friction bearing

**3 Type (Bracket)**

- B** Rigid bracket  
**L** Swivel bracket with mounting plate  
**LF** Swivel bracket with mounting plate, with total lock brake

**4 Coding**

**M** Medium version

d <sub>1</sub> Wheel Ø	b	d <sub>2</sub>	h	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>		m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	m <sub>4</sub>	r	Max. dynamic load capacity in N
						Type L	Type LF						
100	30	9	138	100	85	48	46	45	60	75	80	123	3000
125	38	9	161	100	85	44	44	45	60	75	80	123	3500
150	45	12,5	200	140	110	70	70	73	87	105	105	126	5000
200	50	12,5	250	140	110	70	70	73	87	105	105	126	7300

**Specification**

**Wheel tread / Wheel core**

- Plastic, polyamide (PA)  
• Single part  
• White  
• Hardness 70 Shore D

**Bracket**

Steel sheet metal, zinc plated

**ST**

**Swivel head bracket**

- Dual grease-lubricated ball bearing  
• Dust protection ring on type L / LF  
Plastic, polyethylene (PE)

**Operating temperature** -30 °C to +80 °C

RoHS

Medium duty casters GN 22892 are used in industrial and public indoor areas for moving medium weight carts, for example.

The wheel tread offers low rolling resistance as well as good wear and tearing resistance.

see also...

	Page
<b>GN 22892</b> Wheels (without Bracket)	QVX
<b>GN 22892</b> Medium Duty Casters (Light Version)	QVX
<b>GN 22892</b> Medium Duty Casters (Light Version, with Leveling Foot)	QVX
<b>GN 22892</b> Heavy Duty Casters (Heavy Version)	QVX

**Technical Information**

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

How to order

<b>1</b> d <sub>1</sub>
<b>2</b> Bearing type
<b>3</b> Type (Bracket)
<b>4</b> Coding
<b>5</b> Material (Bracket)

**GN 22892-200-G-L-M-ST**