



elesa
Original design RE.FF

2 Bearing type

- G Friction bearing
- K Ball bearing

3 Type

- A Wheel without bracket



| d ₁ Wheel Ø | b ₁ | b ₂ | | d ₂ | | Recommended ergonomic max. load in N | | Max. static load capacity in N | Max. dynamic load capacity in N | |
|---------------------------|----------------|----------------|----------------|----------------|----------------|--------------------------------------|----------------|--------------------------------|---------------------------------|----------------|
| | | Bearing type G | Bearing type K | Bearing type G | Bearing type K | Bearing type G | Bearing type K | | Bearing type G | Bearing type K |
| 80 | 30 | 39 | 40 | 12 | 8 | 1200 | 1300 | 2200 | 1200 | 1300 |
| 100 | 30 | 44 | 45 | 12 | 8 | 1700 | 2000 | 3000 | 1700 | 2000 |
| 125 | 35 | 44 | 45 | 15 | 8 | 2300 | 2500 | 3500 | 2300 | 2500 |
| 150 | 45 | 59 | 60 | 20 | 12 | 2800 | 3000 | 7000 | 3500 | 3500 |
| 200 | 50 | 59 | 60 | 20 | 12 | 3200 | 3600 | 7500 | 4500 | 4500 |

Specification

Wheel tread

Thermoplastic polyurethane (TPU)

- Injection molded
- Orange
- Hardness 55 Shore D

Wheel core

Plastic, polyamide (PA)

Operating temperature -15 °C to +80 °C

RoHS

Wheels GN 22882 are used in industrial and public indoor areas for moving transport carts, for example.

The wheel tread offers low rolling resistance and high elasticity as well as good wear and tearing resistance.

With bearing type K, the low wear on the ball bearing increases the service life, and the mounting to the inner ring can be accomplished with zero axial backlash.

see also...

| | Page |
|--|------|
| GN 22882 Medium Duty Casters (with Bracket, Light Version) | QVX |
| GN 22882 Medium Duty Casters (with Bracket, Light Version, with Leveling Foot) | QVX |
| GN 22880 Wheels (Wheel Tread Polyurethane, Red) | QVX |
| GN 22884 Wheels (Wheel Tread Polyurethane, Blue) | QVX |

Technical Information

| | |
|--|-----|
| Usage Conditions of Wheels and Casters | QVX |
| Technical Information for Wheels and Casters | QVX |
| Plastic Characteristics | QVX |

How to order

GN 22882-200-K-A

| | |
|---|----------------|
| 1 | d ₁ |
| 2 | Bearing type |
| 3 | Type |

