



elesa  
Original design RLE.F8-N

**2 Bearing type**

G Friction bearing

**3 Type (bracket)**

S Swivel bracket, with mounting plate, with leveling foot

**4 Coding**

L Light version

**1**

d <sub>1</sub> Wheel Ø	b	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	m <sub>4</sub>	r	w ≈ Adjustable range	Max. dynamic load capacity in N
80	30	9	107	95	100	85	40	37	45	60	75	80	120	20	1800
100	30	9	128	118	100	85	35	37	45	60	75	80	120	22	2000
125	38	9	156	150	100	85	37	43	45	60	75	80	120	22	2200

**Specification**

**Wheel tread / Wheel core**

- Plastic, polyamide (PA)
- Single part
- White
- Hardness 70 Shore D

**Bracket**

Steel sheet metal, zinc plated

ST

**Swivel head bracket**

- Dual grease-lubricated ball bearing
- Dust seal
- Plastic, polyethylene (PE)

**Leveling foot**

- Foot
- Plastic, polyamide (PA)
- Glass fiber reinforced, black
- Threaded stud
- Steel zinc plated, blue passivated
- Rubber pad
- Acrylonitrile butadiene rubber (NBR)
- 70 Shore A, black

**Operating temperature** -30 °C to +80 °C

RoHS

Medium duty casters GN 22892 are used in industrial and public indoor areas for positioning and moving mobile workbenches or equipment, for example. The wheel tread offers low rolling resistance as well as good wear and tearing resistance.

The integrated leveling foot can be adjusted in height and ensures stable positioning.

see also...

	Page
GN 22892 Wheels (without Bracket)	QVX
GN 22892 Medium Duty Casters (Light Version)	QVX
GN 22892 Medium Duty Casters (Medium Version)	QVX
GN 22892 Heavy Duty Casters (Heavy Version)	QVX

**Technical Information**

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX

How to order

1	d <sub>1</sub>
2	Bearing type
3	Type (bracket)
4	Coding
5	Material (bracket)

**GN 22892-80-G-S-L-ST**