




elesa
Original design
RE.F8-N / RE.F8-SST-N



2 Bearing type

G Friction bearing

3 Type (Bracket)

- B Rigid bracket
- L Swivel bracket with mounting plate
- LF Swivel bracket with mounting plate, with total lock brake
- R Swivel bracket with center hole
- RF Swivel bracket with center hole, with total lock brake

4 Coding

L Light version

d ₁		b	d ₂	d ₃	d ₄	h		l ₁	l ₂	l ₃	m ₁	m ₂	m ₃	m ₄	r	Max. dynamic load capacity in N
Wheel Ø	Type B / L / R	Type LF / RF				Type B / L / LF	Type R / RF									
65*	-	30	9	12	73	100	100	100	85	40	45	60	75	80	-	1200
80	80	30	9	12	73	107	107	100	85	40	45	60	75	80	120	1800
100	100	30	9	12	73	128	128	100	85	35	45	60	75	80	120	2000
125	125	38	9	12	73	156	156	100	85	37	45	60	75	80	120	2200
150**	150**	45	11	20	102	194	188	140	110	56	73	87	105	105	156	3000
200**	200**	50	11	20	102	240	236	140	110	56	73	87	105	105	156	3000

* Only available in version ST ** Only available in version ST / NI

Specification

Wheel tread / Wheel core

Plastic, polyamide (PA)

- Single part
- White
- Hardness 70 Shore D

Bracket

- Steel sheet metal, zinc plated
- Stainless steel sheet metal AISI 304
- Stainless steel sheet metal AISI 304 with blue wheel

ST
NI
NIB

Swivel head bracket

- Dual grease-lubricated ball bearing
- Dust protection ring on type L / LF
- Plastic, polyethylene (PE)

Operating temperature -30 °C to +80 °C

RoHS

Medium duty casters GN 22892 are used in industrial and public indoor areas for moving lightweight carts, for example. The wheel tread offers low rolling resistance as well as good wear and tearing resistance.

see also...

	Page
GN 22892 Wheels (without Bracket)	QVX
GN 22892 Medium Duty Casters (Light Version, with Leveling Foot)	QVX
GN 22892 Medium Duty Casters (Medium Version)	QVX
GN 22892 Heavy Duty Casters (Heavy Version)	QVX

Technical Information

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX

How to order	1 d ₁
	2 Bearing type
	3 Type (Bracket)
	4 Coding
	5 Material (Bracket)

GN 22892-80-G-RF-L-NI