



elesa
Original design RE.F7-N-HT



2 Bearing type

G Friction bearing

3 Type (Bracket)

- L** Swivel bracket with mounting plate
R Swivel bracket with center hole

4 Coding

L Light version

1 d ₁ Wheel Ø	b	d ₂	d ₃	d ₄	h	l ₁	l ₂	l ₃	m ₁	m ₂	m ₃	m ₄	Max. dynamic load capacity in N
80	35	9	12	73	107	100	85	40	45	60	75	80	1500
100	35	9	12	73	128	100	85	35	45	60	75	80	2000

Specification

Wheel tread / Wheel core

- Plastic, phenolic resin (PF)
- Single part
- Black
- Hardness 90 Shore D

Bracket

- Steel sheet metal, zinc plated **ST**
- Stainless steel sheet metal AISI 304 **NI**

Friction bearing

Plastic, polytetrafluoroethylene (PTFE)

Swivel head bracket

- Dual grease-lubricated ball bearing
- Dust protection ring on type L
- Plastic, polyethylene (PE)

Operating temperature -20 °C to +300 °C

RoHS

Medium duty casters GN 22894 are used in industrial and public indoor areas for moving lightweight carts, for example. They are characterized by their high operating temperature.

see also...

	Page
GN 22894 Wheels (without Bracket)	QVX
GN 22892 Wheels (without Bracket)	QVX
GN 22892 Medium Duty Casters (Light Version)	QVX

Technical Information

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1 d ₁
	2 Bearing type
	3 Type (Bracket)
	4 Coding
	5 Material (Bracket)
GN 22894-80-G-R-L-NI	